

Model ED 56 | Drying and heating chambers with natural convection

The strengths of a BINDER ED series drying chamber include routine drying and sterilization tasks up to 300 °C. Thanks to the natural convection, all thermal processes which use this drying chamber are highly efficient. The ED series ensures fast, uniform drying.

BENEFITS

- · Best energy efficiency on the market
- · Excellent temporal and spatial temperature accuracy
- · USB connection for recording data
- Temperature range up to +300 °C



Model 56



Model 56

MAIN FEATURES

- Temperature range: +5 °C above ambient temperature to +300 °C
- Up to 30% lower energy consumption compared to conventional units on the market
- High temperature accuracy thanks to APT.line™ technology
- Natural convection
- Controller with LCD display
- Electromechanical control of the exhaust air flap

- 2 chrome-plated racks
- Stackable
- Class 2 integrated independent adjustable temperature safety device (DIN 12880) with visual alarm
- Ergonomic handle design
- · USB port for recording data

ORDERING INFORMATION

Interior volume [L]	Voltage	Option model	Version	ArtNo.
	230 V 1~ ph 50/60 Hz	Standard	ED056-230V	9010-0333
5/	120 V 1~ ph 60 Hz	Standard	ED056UL-120V	9010-0334




TECHNICAL DATA

Description	ED056-230V1	EDo56UL-120V ¹
Article Number	9010-0333	9010-0334
Performance Data Temperature		
Temperature range +5 °C above ambient temperature to [°C]	300	300
Temperature variation at 150 °C [± K]	2.3	2.3
Temperature fluctuation at 150 °C [± K]	0.4	0.4
Heating-up time to 150 °C [min]	50	50
Recovery time after 30 seconds door open at 150 °C [min]	19	19
Air change data		
Air change (approx.) at 100 $^{\circ}$ C [x/h]	8	8
Electrical data		
Rated Voltage [V]	230	120
Power frequency [Hz]	50/60	60
Nominal power [kW]	1.05	1.15
Unit fuse [A]	6.3	12.5
Phase (Nominal voltage)	1~	1~
Measures		
Interior volume [L]	57	57
Net weight of the unit (empty) [kg]	42	42
Permitted load [kg]	70	70
Load per rack [kg]	30	30
Wall clearance back [mm]	160	160
Wall clearance sidewise [mm]	100	100
Internal Dimensions		
Width [mm]	360	360
Height [mm]	420	420
Depth [mm]	380	380
Doors		
Unit doors	1	1
Housing dimensions not incl. fittings and connections		
Width net [mm]	560	560
Height net [mm]	625	625
Depth net [mm]	565	565
Environment-specific data		
Energy consumption at 150 °C [Wh/h]	180	180
Fixtures		
Number of shelves (std./max.)	2/4	2/4

¹ All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10%. The temperature data is determined to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.

DIMENSIONS incl. fittings and connections [mm]





OPTIONS

Description	*	ArtNo.
back		
10 mm	01	8012-1282
30 mm	01	8012-0540
50 mm	01	8012-0546
left		
10 mm	01	8012-1275
30 mm	01	8012-1018
50 mm	01	8012-1022
right		
10 mm	01	8012-1268
30 mm	01	8012-1017
50 mm	01	8012-1021
top		
10 mm	01	8012-1262
30 mm	01	8012-0539
50 mm	01	8012-054
100 mm	01	8012-1029
Switchable acoustic alarm, with adjustable limit value on the independent temperature safety device	-	8012-1635
for temperature values (output not adjustable)	02	8012-1623
for temperature; for extending the measurement in center of chamber to include another test temperature	-	8012-1115
for temperature, measurement in center of chamber at specified temperature	_	8012-1134
temperature measurement incl. certificate and 27 measuring points at specified temperature	_	8012-1593
temperature measurement incl. certificate, 15- 18 measuring points at specified temperature	_	8012-1572
	=	8012-1551
with visual alarm (DIN 12880)	-	8012-098
battery-backed	-	8012-1640
made of FKM, silicone-free	-	8012-1008
lockable door handle	-	8012-1664
for Multi Management Software APT-COM™	-	8012-1645
with 15 W light bulb	-	
120 V option model	_	8012-1631
230/240 V option model	_	8012-1627
in accordance with ASTM D5374, definition and protocol according to ambient temperature	-	8012-019
additional flexible Pt 100, interior, for displaying the temperature on the unit display	-	8012-1619
viewing window (triple insulating glass) in door, 240 x 240 mm, and 15 W interior		
120 V option model	_	8012-1059
	back 10 mm 30 mm 50 mm left 10 mm 30 mm 50 mm right 10 mm 30 mm 50 mm right 10 mm 30 mm 50 mm top 10 mm 30 mm 50 mm Switchable acoustic alarm, with adjustable limit value on the independent temperature safety device for temperature values (output not adjustable) for temperature; for extending the measurement in center of chamber to include another test temperature temperature measurement incl. certificate and 27 measuring points at specified temperature temperature measurement incl. certificate, 9 measuring points at specified temperature temperature measurement incl. certificate, 9 measuring points at specified temperature temperature measurement incl. certificate, 9 measuring points at specified temperature temperature measurement incl. certificate, 9 measuring points at specified temperature temperature for this measurement incl. certificate, 9 measuring points at specified temperature temperature measurement incl. certificate, 9 measuring points at specified temperature temperature measurement incl. certificate, 9 measuring points at specified temperature temperature measurement incl. certificate, 9 measuring points at specified temperature with visual alarm (DIN 12880) battery-backed made of FKM, silicone-free lockable door handle for Multi Management Software APT-COM TM with 15 W light bulb 120 V option model 230/240 V option model 130/240 V option model 130/240 V option model 130/240 V option model	back 10 mm o1 30 mm o1 50 mm o1 10 mm o1 30 mm o1 50 mm o1 50 mm o1 50 mm o1 30 mm o1 30 mm o1 50 mm o1 50 mm o1 10 mm o1 30 mm o1 50 mm o1 30 mm o1 50 mm o1 <

ACCESSORIES

Designation	Description	*	ArtNo.
APT-COM™ 4 BASIC- Edition	for simple logging and documentation requirements with up to 5 networked units.		
	version 4, BASIC edition	-	9053-0039

^{*} Notes > See last page



Designation	Description	*	ArtNo.
APT-COM™ 4 GLP- Edition	for working under GLP-compliant conditions. Measured values are documented in a tamper-proof way in line with the requirements of FDA Regulation 21 CFR 11.		
Euition	version 4, GLP edition	-	9053-0042
APT-COM™ 4	convenient unit and user management built on the BASIC edition. Suitable for networking up to 100 units.		
PROFESSIONAL-Edition	version 4, PROFESSIONAL edition	-	9053-0040
Data Logger Kit	T 350: For continuous temperature logging from 0 °C to 350 °C; kit includes 1 data logger, Pt 100 sensor with 2 m extension cable and 1 magnetic fixture for mounting to the BINDER unit		8012-0714
Data Logger Software	LOG ANALYZE software kit, configuration and evaluation software for all BINDER Data Logger Kits (incl. USB data cable)	-	8012-082
Ethernet interface	for Multi Management Software APT-COM™	-	8012-1645
pH-neutral detergent	concentrated, for gentle remove of residual contaminants; 1 kg	-	1002-0016
	IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature, CO_2 , O_2 , pressure, depending on unit		
	Digital in PDF format	-	7057-0001
Ouglification documents	Hard copy inside folder	-	7007-000
Qualification documents	IQ/OQ/PQ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ; parameters: temperature, CO_2 , O_2 – or pressure, depending on unit		
	Digital in PDF format	-	7057-000
	Hard copy inside folder	-	7007-000
Rack	chrome plated	-	6004-0174
Nack	stainless steel	-	6004-0158
Rack, heavy load	Stainless steel, max. load per rack 50 kg	-	6004-025
Rubber pads	set anti-slip feet	-	8012-1887
Shelf, perforated	Stainless steel	-	6004-019
Table on castors	stable cart, casters with locking brakes, dimensions: W 1,000 x D 800 x H 780 mm	-	9051-0018
* Notes > See last nage			

^{*} Notes > See last page

SERVICES

Designation	Description	*	ArtNo.
Installation services			
Unit commissioning	Connect the unit to the customer-side connections (electricity, water, wastewater, gas), basic functions check, brief operating instructions. (excl.: unpacking, setup, controller instructions, programming, installation work)	05	DL10-0100
Unit instructions	Instruction regarding operating principle and basic functions of the unit, operation of the control electronics including programming	05	DL10-0500
Maintenance contracts			
Maintenance services			
BRONZE 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts	05	DL20-0710
GOLD 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, replacement of wear parts, calibration of one test temperature specified by the user in the center of the usable space, including certificate	05	DL20-0910
Maintenance	One-off maintenance service in accordance with maintenance schedule. Visual inspection of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate	05	DL20-0200
SILVER 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, calibration of one test temperature specified by the user in the center of the usable space, without certificate	05	DL20-0810
Calibration services			
Calibration certificate, temperature	Calibration of one (1) test temperature specified by the user in center of chamber, including certificate	03, 04, 05	DL30-0101
	Extension of calibration of one (1) additional test temperature specified by the user in the center of the usable space, including certificate	03, 04, 05	DL30-0102
Measurement of air exchange rate	including certificate (in accordance with ASTM D5374)	03, 04, 05	DL33-0000
* Notes > See last page			

^{*} Notes > See last page



Designation	Description	*	ArtNo.
Temperature measurement, 18 measuring points	Temperature measurement with 18 measuring points with a set value specified by the user, including certificate	03, 04, 05	DL30-0118
Temperature measurement, 27 measuring points	Temperature measurement with 27 measuring points with a set value specified by the user, including certificate	03, 04, 05	DL30-0127
Temperature measurement, 9 measuring points	Temperature measurement with 9 measuring points with a set value specified by the user, including certificate	03, 04, 05	DL30-0109
Validation services			
Execution of IQ/OQ	Execution of IQ/OQ in accordance with qualification folder	05	DL40-0100
Execution of IQ/OQ/PQ	Execution of IQ/OQ/PQ in accordance with qualification folder	05	DL44-0500
Warranty service			
1-year warranty extension	The warranty is extended by 1 year from the delivery date, wear parts are excluded	-	DL50-0010

^{*} Notes > See last page



NOTES

- Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge. UL mark is not granted when this option is used.
- 02
- Sensor calibration is performed in an accredited calibration laboratory. 03
- Calibration is performed according to the BINDER factory standard.
- Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not include a country-specific added fee (available on request).

BINDER GmbH

Tuttlingen, Germany TEL +49 7462 2005 0 FAX +49 7462 2005 100 info@binder-world.com www.binder-world.com

BINDER Asia Pacific (Hong Kong) Ltd.

Kowloon, Hong Kong, P.R. China TEL +852 39070500 FAX +852 39070507 asia@binder-world.com www.binder-world.com

BINDER Environmental Testing Equipment (Shanghai) Co., Ltd. Shanghai, P.R. China TEL +86 21 685 808 25 FAX +86 21 685 808 29 china@binder-world.com www.binder-world.com

Representative Office for CIS

Moscow, Russia TEL +7 495 988 15 16 FAX +7 495 988 15 17 russia@binder-world.com www.binder-world.com

BINDER Inc.

Bohemia, NY, USA TEL +1 631 224 4340 FAX +1 631 224 4354 usa@binder-world.com www.binder-world.us