lab consumables & labware



BUNSEN BURNER "standard type"

- Most common used bunsen burner with flame adjustment.
- ➤ Can be used with all gases such as neutral gas, butane gas and coal gas.
- ➤ Offers practical control of flame from very slow heating to rapid boiling with an adjustable air and gas regulation ring.
- ➤ Precise flame adjustment is guaranteed by a screw driven gas control knob.

catalogue	pack
number	quantity
050.01.001	1 piece



CAMP BURNER

Can be used where connection to a gas pipe line is not existing. Supplied without gas cartridge.

catalogue	pack
number	quantity
050.01.004	1 piece



BUNSEN BURNER "advanced type"

- ➤ Preferably used if higher heating capacity is required.
- ➤ Can be used with all gases such as neutral gas, butane gas and coal gas.
- > Offers practical control of flame from very slow heating to rapid boiling with an adjustable air and gas regulation ring.
- ➤ Precise flame adjustment is guaranteed by a screw driven gas control knob.

catalogue	pack
number	quantity
050.01.002	1 piece



BUNSEN BURNER "meker type"

- For very high heating heating up to 1700°C is required.
- ➤ Can be used with all gases such as neutral gas, butane gas and coal gas.
- > Offers practical control of flame from very slow heating to rapid boiling with an adjustable air and gas regulation ring.
- ➤ Precise flame adjustment is guaranteed by a screw driven gas control knob.

catalogue	pack
number	quantity
050.01.003	1 piece



BUNSEN BURNER STABILIZER

- There is always a tilt over risk for bunsen burners.
- ➤ Bunsen burner stabilizer provides a very stable and robust additional base and holds the attached bunsen burner firmly avoiding above mentioned risk.
- The nest perfectly fits to the bases of bunsen burners with catalogue no: 050.01.002 and 050.01.003.
- First insert the bunsen burner into the stabilizer nest. Then stabilize the bunsen burner by fixing the provided screw tightly.

catalogue	pack
number	quantity
050.09.001	1 piece



- be used where connection to a gas pipe line is not existing.
- Precise flame adjustment by a screw driven gas control knob.
- > Supplied without gas cartridge. Kindly order gas cartridge separately.

blow lamp	spare gas pack cartrice quantity	
050.02.001	050.03.001 1 piece	



HOSES - "for bunser burners"

➤ Manufactured from extra thick walled rubber. Specially designed to be used with bunsen burners. Reinforced ends fits perfect to the bunsen

burner at one side and the gas tap at the other side assuring gas leakage free connection.

catalogue number	pack quantity
050.08.075	1 piece
050.08.100	1 piece